

Nanocrystalline Material (FINEMET)

datasheet

Nanocrystalline materials are emerging soft magnetic materials that possess grain sizes on the order of a billionth of a meter and possess extremely useful magnetic properties. These materials fill the gap between amorphous materials (without any long-range order) and conventional (coarse-grained) materials. Nanocrystalline alloys are materials on the basis of Fe (iron), Si (silicon), and B (boron), with additions of Nb (niobium) and Cu (copper). Typically, they are produced through a rapid solidification process as a thin, ductile ribbon. Initially the ribbon is in the amorphous state, then crystallized in a subsequent heat treatment to promote nano-crystallization (~10-20 nanometers). Once nano-crystallized, they exhibit low core loss and magnetostriction, while maintaining high saturation induction and permeability. A variety of forms can be manufactured, including toroidal, rectangular, racetrack and block cores.

Date: September 2018
Revision 0.1

© U.S. Department of Energy - National Energy Technology Laboratory



Fig. 1: Core under test
(Nano-crystalline core)

Nano-crystalline core

Dimensions

Table 1: Core dimensions

Description	Symbol	Finished dimension (mm)
Width of core	A	180
Height of core	B	240
Depth of core (or cast width)	D	30
Thickness or build	E	50
Width of core window	F	80
Height of core window	G	140




Fig. 2: Illustration of core dimensions

Acknowledgement

This technical effort was performed in support of the National Energy Technology Laboratory's ongoing research in DOE's The Office of Electricity's (OE) Transformer Resilience and Advanced Components (TRAC) program under the RES contract DE-FE0004000.

Disclaimer

This project was funded by the Department of Energy, National Energy Technology Laboratory, an agency of the United States Government, through a support contract with AECOM. Neither the United States Government nor any agency thereof, nor any of their employees, nor AECOM, nor any of their employees, makes any warranty, expressed or implied, or assumes any legal liability or responsibility for the accuracy, completeness, or usefulness of any information, apparatus, product, or process disclosed, or represents that its use would not infringe privately owned rights. Reference herein to any specific commercial product, process, or service by trade name, trademark, manufacturer, or otherwise, does not necessarily constitute or imply its endorsement, recommendation, or favoring by the United States Government or any agency thereof. The views and opinions of authors expressed herein do not necessarily state or reflect those of the United States Government or any agency thereof.

Magnetic Characteristics

Table 2: Magnetic characteristics

Description	Symbol	Typical value	Unit
Effective area	A_e	1,170	mm ²
Mean magnetic path length ¹	L_m	583	mm
Mass (before impregnation)		5.234	kg
Mass (after impregnation)		5.528	kg
Lamination thickness		0.0007 (0.0178)	inch (mm)
Chemistry		Fe _{73.5} Nb ₃ Si _{15.5} B ₇ Cu ₁	
Grade		Nano-crystalline	
Anneal		Field Anneal	
Impregnation		100% Solids Epoxy	
Supplier		MK Magnetics	
Part number		4216MDT-B	

Measurement Setup





Fig. 3: Arbitrary waveform core loss test system (CLTS) (a) conceptual setup (b) actual setup

The BH curves, core losses, and permeability of the core under test (CUT) are measured with an arbitrary waveform core loss test system (CLTS), which is shown in Fig. 3. Arbitrary small signal sinusoidal waveforms are generated from a function generator, and the small signals are amplified via an amplifier.

¹ Mean magnetic path length is computed using the following equation. OD and ID are outer and inner diameters, respectively.
$$L_m = \frac{\pi(OD - ID)}{\ln\left(\frac{OD}{ID}\right)}$$

Two windings are placed around the core under test. The amplifier excites the primary winding, and the current of the primary winding is measured, in which the current information is converted to the magnetic field strengths H as

$$H(t) = \frac{N_p \cdot i(t)}{l_m} , \quad (1)$$

where N_p is the number of turns in the primary winding. A dc-biasing capacitor is inserted in series with the primary winding to provide zero average voltage applied to the primary winding.

The secondary winding is open, and the voltage across the secondary winding is measured, in which the voltage information is integrated to derive the flux density B as

$$B(t) = \frac{1}{N_s \cdot A_e} \int_0^t v(\tau) d\tau , \quad (2)$$

where N_s is the number of turns in the secondary winding, and T is the period of the excitation waveform.

Fig. 4 illustrates three different excitation voltage waveforms and corresponding flux density waveforms. When the excitation voltage is sinusoidal as shown in Fig. 4(a), the flux is also a sinusoidal shape. When the excitation voltage is a two-level square waveform as shown in Fig. 4(b), the flux is a sawtooth shape. The average excitation voltage is adjusted to be zero via the dc-biasing capacitor, and thus, the average flux is also zero. When the excitation voltage is a three-level square voltage as shown in Fig. 4(c), the flux is a trapezoidal shape. The duty cycle is defined as the ratio between the applied high voltage time and the period. In the sawtooth flux, the duty cycle can range from 0% to 100%. In the trapezoidal flux, the duty cycle range from 0% to 50%. At 50% duty cycles, both the sawtooth and trapezoidal waveforms become identical.

It should be noted that only limited ranges of the core loss measurements are executed due to the limitations of the amplifier, such as $\pm 75V$ & $\pm 6A$ peak ratings and $400V/\mu s$ slew rate. The amplifier model number is HSA4014 from NF Corporation. For example, it is difficult to excite the core to high saturation level at high frequency due to limited voltage and current rating of the amplifier. Therefore, the ranges of the experimental results are limited.

Additionally, the core temperature is not closely monitored; however, the core temperature can be assumed to be near room temperature.




Fig. 4: Excitation voltage waveforms and corresponding flux density waveforms (a) Sinusoidal flux, (b) Sawtooth flux, and (c) Trapezoidal flux

Anhyseritic BH Curves

Fig. 5 illustrates the measured low frequency BH loops at 2 kHz. Using the BH loop, the anhyseritic BH curve is fitted. The anhyseritic BH curves can be computed as a function of field intensity H using the follow formula.

$$B = \mu_H(H)H$$

$$\mu_H(H) = \mu_0 + \sum_{k=1}^K \frac{m_k}{h_k} \frac{1}{1 + |H/h_k|^{n_k}} \quad (3)$$




Fig. 5: Low frequency BH loops (excitation at 500 Hz, $N_p = 6$, $N_s = 6$)

Similarly, the anhyseritic BH curves can be computed as a function of flux density B using the follow formula.

$$B = \mu_B(B)H$$

$$\mu_B(B) = \mu_0 \frac{r(B)}{r(B) - 1}$$

$$r(B) = \frac{\mu_r}{\mu_r - 1} + \sum_{k=1}^K \alpha_k |B| + \delta_k \ln(\varepsilon_k + \zeta_k e^{-\beta_k |B|}) \quad (4)$$

$$\delta_k = \frac{\alpha_k}{\beta_k}, \varepsilon_k = \frac{e^{-\beta_k \gamma_k}}{1 + e^{-\beta_k \gamma_k}}, \zeta_k = \frac{1}{1 + e^{-\beta_k \gamma_k}}$$

Table 3 and Table 4 lists the anhyseritic curve coefficients for eqs. (3) and (4), respectively.

The core anhyseritic characteristic models in eqs. (3) and (4) are based on the following references.

Scott D. Sudhoff, "Magnetics and Magnetic Equivalent Circuits," in *Power Magnetic Devices: A Multi-Objective Design Approach*, 1, Wiley-IEEE Press, 2014, pp.488-

G. M. Shane and S. D. Sudhoff, "Refinements in Anhyseritic Characterization and Permeability Modeling," in *IEEE Transactions on Magnetics*, vol. 46, no. 11, pp. 3834-3843, Nov. 2010.

The estimation of the anhyseritic characteristic is performed using a genetic optimization program, which can be found in the following websites:

https://engineering.purdue.edu/ECE/Research/Areas/PEDS/go_system_engineering_toolbox

Table 3: Anhyseritic curve coefficients for B as a function of H

k	1	2	3	4
m_k	1.45432290901190	-0.787469528017856	0.305816513846983	-0.100099666071160
h_k	1.66901849037468	4.53941231474504	16.3984489615004	2.21434113438350
n_k	1	1.39181845814425	1.91929608345426	2.47225983230501

Table 4: An hysteretic curve coefficients for H as a function of B

k	1	2	3	4
μ_r	122403.680741993			
α_k	0.601590372006389	0.0373154057929699	0.0371340984781102	0.00547195463929012
β_k	49.0941919818141	6.05165057248446	342.771453167956	26.7566654427740
γ_k	1.43228670933891	2.10625323925708	1.41322170444317	1.30002822552914
δ_k	0.0122537992320810	0.00616615340658217	0.000108334863171685	0.000204508093543767
ε_k	2.89556194654586e-31	2.91304528523862e-06	4.19291980155985e-211	7.82200715654711e-16
ζ_k	1	0.999997086954715	1	0.999999999999999

Fig. 6 illustrates the measured BH curve and fitted anhysteretic BH curves as functions of H and B using the coefficients from Table 3 and Table 4. Fig. 7 and Fig. 8 illustrates the absolute relative permeability as functions of field strength H and flux density B , respectively. Fig. 9 illustrates the incremental relative permeability.




Fig. 6: Measured BH curve and fitted anhysteretic BH curve as functions of H and B




Fig. 7: Absolute relative permeability as function of field strength H




Fig. 8: Absolute relative permeability as function of flux density B




Fig. 9: Incremental relative permeability

Core Losses

Core losses at various frequencies and induction levels are measured using various excitation waveforms. Based on measurements, the coefficients of the Steinmetz's equation are estimated. The Steinmetz's equation is given as

$$P_w = k_w \cdot (f / f_0)^\alpha \cdot (B / B_0)^\beta \quad (5)$$

where P_w is the core loss per unit weight, f_0 is the base frequency, B_0 is the base flux density, and k_w , α , and β are the Steinmetz coefficients from empirical data. In the computation of P_w , the weight before impregnation in Table 2 is used, the base frequency f_0 is 1 Hz, and the base flux density B_0 is 1 Tesla.

Fig. 10 illustrates the measured BH curve at different frequencies. The field strength H is kept near constant for all frequency. At 100 Hz and 200 Hz excitations, the BH curve is similar, which indicates that the hysteretic losses are the dominant factor at frequencies below 100 Hz. As frequency increases, the BH curves become thicker, which indicates that the eddy current and anomalous losses are becoming larger.




Fig. 10: BH curve as a function of frequency ($N_p = 5$, $N_s = 5$, $I_p = 5.0A$)

Table 5 lists the Steinmetz coefficients at different excitation conditions, and Fig. 11 illustrates the core loss measurements and estimations via Steinmetz equation.

Table 5: Steinmetz coefficients

	k_w	A	β
sine	0.000384131650964337	1.20766039986774	1.64556336546660
Sawtooth/Trapezoidal 50% duty	0.000452111623139207	1.17545462809301	1.71254312973925
Sawtooth 30% duty	0.000403105359275290	1.19488976314939	1.72838701795985
Sawtooth 10% duty	0.000233083038257796	1.30172183993727	1.77164778257915
Trapezoidal 30% duty	0.000308954249222202	1.24873999771952	1.62296340616880
Trapezoidal 10% duty	0.000291680994530371	1.30751253805291	1.74053549042445









Fig. 11: Core loss measurements and estimations via Steinmetz equation: (a) Sine (b) Sawtooth/Trapezoidal 50% duty (c) Sawtooth 30% duty (d) Sawtooth 10% duty (e) Trapezoidal 30% duty (f) Trapezoidal 10% duty

Core Permeability

The permeability of the core is measured as functions of flux density and frequency. Fig. 12 illustrates the measured absolute relative permeability μ_r values, which is defined as

$$\mu_r = \frac{B_{peak}}{\mu_0 \cdot H_{peak}} \quad (6)$$

where B_{peak} and H_{peak} are the maximum flux density and field strength at each measurement point.










Fig. 12a: Left column: relative permeability as a function of flux density and frequency, Right column: BH loop at the maximum B of the corresponding frequency (a) Sine (b) Sawtooth/Trapezoidal 50% duty (c) Sawtooth 30% duty



(d)



(e)



(f)

Fig. 12b: Left column: relative permeability as a function of flux density and frequency, Right column: BH loop at the maximum B of the corresponding frequency (d) Sawtooth 10% duty (e) Trapezoidal 30% duty (f) Trapezoidal 10% duty

